

243095-5



Stainless Steel Hardware Kit for 4 mm, 3/8 in, 5/8 in, 1/2 in or 7/8 in Block style hangers, includes 3/8 in bolts and hardware, 137.16 mm (5.4 in) length

Product Classification

Product Type	Hardware kit
Product Brand	HELIAX®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Thread Size 3/8 in

Dimensions

Maximum Stack Height	2
Length	137.16 mm 5.4 in
Nominal Size	1/2 in 7/8 in

Material Specifications

Material Type Stainless steel 304

Packaging and Weights

Height, packed	149.86 mm 5.9 in
Width, packed	63.5 mm 2.5 in
Length, packed	63.5 mm 2.5 in
Included	Fifty flat washers Ten 3/8 in threaded rods Thirty hex nuts Twenty lock washers
Packaging quantity	10
Weight, gross	1.129 kg 2.49 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

243095-5

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power