

# 245314-240

---



Single Entrance Panel for elliptical waveguide 240

## Product Classification

**Product Type** Entrance panel

## General Specifications

**Color** Gray

**Entry Panel Port Size** 101.6 mm | 4 in

**Number of Ports** 1

**Panel Type** Single

## Dimensions

**Height** 76.2 mm | 3 in

**Width** 127 mm | 5 in

**Waveguide Size** WR42 | WG20 | R220

## Material Specifications

**Material Type** Aluminum

## Environmental Specifications

**Weather Resistance Test Method** 04AS00-03.9.0 | IEC 60529.14.2

## Packaging and Weights

**Height, packed** 180.34 mm | 7.1 in

**Width, packed** 180.34 mm | 7.1 in

**Length, packed** 180.34 mm | 7.1 in

**Included** Boot | Plate

# 245314-240

---

**Packaging quantity** 1  
**Weight, gross** 0.91 kg | 2.006 lb

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

- 204673-1 - 1 Port Entrance Panel 1 x 1
- WGB4-240 - Boot Assembly, 4 in, for elliptical waveguide 240



1 Port Entrance Panel 1 x 1

## Product Classification

<b>Product Type</b>	Entrance panel
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Color</b>	Gray
<b>Entry Panel Port Size</b>	101.6 mm   4 in
<b>Number of Ports</b>	1
<b>Panel Type</b>	Single

## Dimensions

<b>Height</b>	177.8 mm   7 in
<b>Width</b>	177.8 mm   7 in

## Material Specifications

<b>Material Type</b>	Aluminum
----------------------	----------

## Environmental Specifications

<b>Weather Resistance Test Method</b>	04AS00-03.9.0   IEC 60529:2001, IP66
---------------------------------------	--------------------------------------

## Packaging and Weights

<b>Height, packed</b>	177.8 mm   7 in
<b>Width, packed</b>	177.8 mm   7 in
<b>Length, packed</b>	40.64 mm   1.6 in
<b>Included</b>	Entry cap   Hardware   Port
<b>Packaging quantity</b>	1

# 204673-1

---

**Weight, gross**

0.28 kg | 0.617 lb

## Regulatory Compliance/Certifications

**Agency**

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

**Classification**

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant



# WGB4-240

---



Boot Assembly, 4 in, for elliptical waveguide 240

## Product Classification

**Product Type** Boot assembly

## General Specifications

**Cable Type** Elliptical waveguide  
**Cables per Cushion** 1  
**Color** Black

## Dimensions

**Width** 101.6 mm | 4 in  
**Length** 76.2 mm | 3 in  
**Waveguide Size** WR42 | WG20 | R220

## Material Specifications

**Material Type** EPDM rubber

## Environmental Specifications

**UV Resistance Test Method** MIL-STD-810E, Procedure 11, Method 557  
**Weather Resistance Test Method** 04AS00-03.9.52 | IEC 60529:2001, IP66

## Packaging and Weights

**Included** Boot | Cushion  
**Packaging quantity** 1

## Regulatory Compliance/Certifications

**Agency**                      **Classification**

# WGB4-240

---

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

