33938-5

Single Entrance Panel for 5 in coaxial cable

Product Classification

Product Type Entrance panel

Ordering Note CommScope® non-standard product

General Specifications

Color Gray

Entry Panel Port Size 162.56 mm | 6.4 in

Number of Ports 1

Panel Type Single

Dimensions

 Height
 177.8 mm | 7 in

 Width
 76.2 mm | 3 in

Nominal Size 5 in

Material Specifications

Material Type Aluminum

Environmental Specifications

Weather Resistance Test Method 04AS00-03.9.0 | IEC 60529:2001, IP66

Packaging and Weights

 Height, packed
 304.8 mm | 12 in

 Width, packed
 76.2 mm | 3 in

 Length, packed
 304.8 mm | 12 in

Included Boot | Clamp | Plate

Packaging quantity 1

Weight, gross 2.92 kg | 6.437 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

33938-5

ISO 9001:2015 REACH-SVHC

ROHS



Designed, manufactured and/or distributed under this quality management system Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant

