912MCLICK



Miniature Click-on Hanger for 9–12 mm cable

Product Classification

Product Type Hanger kit

Ordering Note CommScope® standard product (Global)

General Specifications

Cables per Hanger 2

Color Black

Hanger TypeClick-on hangerMountingM8 through hole

Dimensions

Maximum Stack Height 3

 Height
 38.1 mm | 1.5 in

 Width
 20.1 mm | 0.791 in

 Length
 42.9 mm | 1.689 in

Compatible Cable Diameter Range 9–12 mm

Compatible Diameter, maximum12 mm | 0.472 inCompatible Diameter, minimum9 mm | 0.354 inNominal Size1/4 in | 3/8 in

Electrical Specifications

Return Loss Effect, maximum 0.1 dB

DTF Effect, maximum 0.1 dB

Material Specifications

Material Type Engineered plastic

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Page 1 of 2

912MCLICK

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Environmental Strength CapabilityDouble cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

 Height, packed
 15.2 cm | 5.984 in

 Width, packed
 20.3 cm | 7.992 in

 Length, packed
 2.5 cm | 0.984 in

Packaging quantity 10

Weight, gross 0.13 kg | 0.287 lb

Regulatory Compliance/Certifications

Agency	Classification
Agency	Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power