

CL7145-000 | MWTM-25/8-60/U(S250)



MWTM Medium-Wall Heat-Shrinkable Tubing kit, 25 mm/8 mm Shrink ratio, 60 mm long, uncoated, 250 pcs

- Flexible in use and installation due to its high shrink ratio
- Hotmelt adhesive version used where high mechanical and sealing performance is required
- Uncoated version used as an electrical insulator

Product Classification

Regional Availability	EMEA
Product Type	Heat shrink tubing, medium wall
Product Series	MWTM

General Specifications

Color	Black
Sealant Type	Uncoated

Dimensions

Length	60 mm 2.362 in
Expanded Inside Diameter, minimum	25 mm 0.984 in
Recovered Inside Diameter, maximum	8 mm 0.315 in
Recovered Wall Thickness, minimum	2 mm 0.079 in

Material Specifications

Material Type	Polyolefin
----------------------	------------

Environmental Specifications

Environmental Space	Aerial Ducted
----------------------------	-----------------

Packaging and Weights

Packaging quantity	250
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

CL7145-000 | MWTM-25/8-60/U(S250)

Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

**Classification**

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant