

CU4787-000 | FIST-FDASA2-4M120ANN-L



FIST® Fiber Splice Tray with Field Installable DWDM, 4 Channels, Multiplexing, 1561.42nm starting wavelength, 100GHz channel spacing, all fibers at left side

Product Classification

Regional Availability	EMEA
Product Type	DWDM splice tray
Product Brand	FIST®
Product Series	FIST-FDASA2

General Specifications

Application	For use with FIST fiber splice closures For use with FIST panels
Interface, Input	Stub tail
Interface, Output	Stub tail

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

