

# DD6594-000 | FOSC-OC-6DBD1201NN2T-U23

---

FOSC® A-TRAY-24 type, DWDM, 8 channels + upgrade port, demux, 1561.42 nm starting wavelength, 100 GHz channel spacing



## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	DWDM splice tray
<b>Product Brand</b>	FOSC®
<b>Product Series</b>	FOSC-OC

## General Specifications

<b>Application</b>	For use in FOSC closures
<b>Interface, Input</b>	Stub tail
<b>Interface, Output</b>	Stub tail

## Dimensions

<b>Height</b>	9.2 mm   0.362 in
<b>Depth</b>	10.67 mm   0.42 in

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted

