

EWSH-220



Universal Snap-in Hanger for elliptical waveguide 220

Product Classification

Product Type Hanger kit

General Specifications

Cable Type Elliptical waveguide

Cables per Hanger 1

Color Silver

Hanger Type Snap-in hanger

Mounting 3/4 in through hole

Dimensions

Height 40.9 mm | 1.61 in

Width 42.9 mm | 1.689 in

Length 72.9 mm | 2.87 in

Compatible Diameter, maximum 31 mm | 1.22 in

Compatible Diameter, minimum 23.1 mm | 0.909 in

Waveguide Size WR42 | WG20 | R220

Electrical Specifications

Return Loss Effect, maximum 0.1 dB

DTF Effect, maximum 0.1 dB

Material Specifications

Material Type Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

EWSH-220

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Environmental Strength Capability	Double cable weight

Packaging and Weights

Height, packed	20 cm 7.874 in
Width, packed	20 cm 7.874 in
Length, packed	20 cm 7.874 in
Packaging quantity	10
Weight, gross	1.6 kg 3.527 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system