

IC-1010-B



Ice Canopy, 10 ft x 10 ft, four 13 ft 4 in burial pipes

Product Classification

Product Type Ice canopies and shields

General Specifications

Pipe, quantity 4

Dimensions

Height 4064 mm | 160 in


Width 3048 mm | 120 in

Length 3048 mm | 120 in

Pipe Length 4064 mm | 160 in

IC-1010-B

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Hardware | Legs | Safety grating

Packaging quantity 1

Weight, net 375 kg | 826.732 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

ROHS

Classification

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant/Exempted

IC-1010-B

UK-ROHS

Compliant/Exempted



Included Products

- MF-130 - Direct Burial Pipe Column, 13 ft 4 in
- WB-CY210 - Safety Grated Waveguide Bridge Channel, 24 in x 10 ft