760251229 | FACT-MMDL5H-A



FACT® MPO Module, left sided, LC at front side, 2x12 fiber MPO at rear side, Ultra Low Loss (ULL) multimode OM5, wiring method A straight

- Offers the same craft-friendly interface for LC and SC connectors as the cabled module
- Allow installers to connect an MPO trunk cable to turn up services in rapid installation applications

Product Classification

Regional Availability Asia | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber module

Product Brand FACT®
Product Series FACT

General Specifications

Functionality Breakout

Application For Use with FACT NG4 Universal Chassis

Body Style Left orientation

Color, bootBlackColor, housingBlack

Color, rearLime greenInterface, frontLC/UPCInterface Feature, frontDuplexInterface Color, frontLime green

Interface, rear MPO

Interface Feature, rear Female | Key up/down | Pinned

Interface Color, rearLime greenPolarityMethod A

Total Fibers, quantity 24

Total Ports, quantity, front 12

Total Ports, quantity, rear 2

Dimensions



760251229 | FACT-MMDL5H-A

 Height
 13.21 mm | 0.52 in

 Width
 159.77 mm | 6.29 in

 Depth
 122.68 mm | 4.83 in

Optical Specifications

Fiber ModeMultimodeFiber TypeOM5

Insertion Loss, maximum0.4 dBInsertion Loss, typical0.32 dBReturn Loss, minimum27 dB

Environmental Specifications

Operating Temperature-5 °C to +40 °C (+23 °F to +104 °F)Storage Temperature-5 °C to +50 °C (+23 °F to +122 °F)

Relative Humidity Up to 85%, non-condensing

Packaging and Weights

Packaging quantity

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

