

#### Double Click-on Hanger for 1/2 in coaxial cable

#### **Product Classification**

Product Type Hanger kit

Ordering Note CommScope® standard product (Global)

General Specifications

Cables per Hanger 2

**Color** Black

**Hanger Type** Click-on hanger

**Mounting** Mounting hole clearance for 3/8, 16 UNC or M10 threaded rod

**Dimensions** 

Maximum Stack Height 3

 Height
 51.1 mm | 2.012 in

 Width
 45 mm | 1.772 in

 Length
 88.9 mm | 3.5 in

 Compatible Cable Diameter Range
 15.2–16.3 mm

Compatible Diameter, maximum16.3 mm | 0.642 inCompatible Diameter, minimum15.2 mm | 0.598 in

Nominal Size 1/2 in

**Electrical Specifications** 

 Return Loss Effect, maximum
 0.1 dB

 DTF Effect, maximum
 0.1 dB

Material Specifications

Material Type Engineered plastic

Page 1 of 2

# L4CLICK

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

### **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

Environmental Strength Capability Double cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

 Height, packed
 19 cm | 7.48 in

 Width, packed
 8 cm | 3.15 in

 Length, packed
 17 cm | 6.693 in

Packaging quantity 10

**Weight, gross** 0.26 kg | 0.573 lb

## Regulatory Compliance/Certifications

#### Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



#### \* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

