

RM-SS-L2



Ring Mount Tie Back Support Kit

Product Classification

Product Type Ring mount

General Specifications

Mounting Monopole, 762–1524 mm (30–60 in) OD

Sectors, quantity 1

Dimensions

Height 10 in | 254 mm

Width 48 in | 1,219.2 mm

Length 48 in | 1,219.2 mm

Mounting Diameter, maximum 60 in | 1524 mm

Mounting Diameter, minimum 30 in | 762 mm

Mounting Circumference, maximum 188.4 in | 4,785.36 mm

Mounting Circumference, minimum 94.2 in | 2,392.68 mm

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Angle | Hardware | Mount

Packaging quantity 1

Weight, net 90.7 kg | 199.959 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

RM-SS-L2

ROHS

Compliant

UK-ROHS

Compliant

