

# RM-SS-M2

---



## Ring Mount Tie Back Support Kit

### Product Classification

**Product Type** Ring mount

### General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD

**Sectors, quantity** 1

### Dimensions

**Height** 10 in | 254 mm

**Width** 48 in | 1,219.2 mm

**Length** 48 in | 1,219.2 mm

**Mounting Diameter, maximum** 50 in | 1270 mm

**Mounting Diameter, minimum** 15 in | 381 mm

**Mounting Circumference, maximum** 157.1 in | 3,990.34 mm

**Mounting Circumference, minimum** 47.1 in | 1,196.34 mm

### Material Specifications

**Material Type** Hot dip galvanized steel

### Packaging and Weights

**Included** Angle | Hardware | Mount

**Packaging quantity** 1

**Weight, net** 79.4 kg | 175.047 lb

### Regulatory Compliance/Certifications

#### Agency

CHINA-ROHS

REACH-SVHC

#### Classification

Below maximum concentration value

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

# RM-SS-M2

---

ROHS                      Compliant  
UK-ROHS                Compliant

