DLX-SC-CONV-25

DLX to SC/UPC Converter

• Hardened drop cables simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America	
Product Type	Fiber converter	
Product Brand	DLX®	
Product Series	FHD	

General Specifications

Interface, Connector A	Hardened mini-size DLX
Interface, Connector B	SC/UPC

Optical Specifications

Insertion Loss, maximum	0.5 dB
Return Loss, minimum	65 dB

Environmental Specifications

Operating Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Qualification Standards	Telcordia GR-326-CORE

25

Packaging and Weights

Packaging quantity

Page 1 of 1

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 21, 2024

