

760249095



Kit, SMB, 2 Fiber Ports, 2 Power Ports, Beige

Powered Fiber Cable Surface Mount Box Kit, 2 Fiber Ports, 2 Power Ports, Beige

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Surface mount module
Product Series	SL Series SLX Series

General Specifications

Application	Powered fiber
Color	Beige
Interface Feature, front	Two wire terminals (2) fiber Duplex (2)
Mounting	Surface
Outlet Orientation	Flat
Port Marking Type	Label
Total Ports, quantity	4

Dimensions

Height	38 mm 1.496 in
Width	142.3 mm 5.602 in
Depth	116.2 mm 4.575 in

Electrical Specifications

Input Power	100 W (NEC Class 2)
Input Voltage	30 Vac 60 Vdc
Electrical Safety Standard	CB IEC 60950-1 IEC 62368-1 UL cUL

Material Specifications

Material Type	Polycarbonate
----------------------	---------------

Environmental Specifications

760249095

Environmental Space Indoor
Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 1
Weight, net 0.149 kg | 0.328 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

