# 760249095



Kit, SMB, 2 Fiber Ports, 2 Power Ports, Beige

Powered Fiber Cable Surface Mount Box Kit, 2 Fiber Ports, 2 Power Ports, Beige

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Surface mount module
Product Series	SL Series   SLX Series

#### General Specifications

Application	Powered fiber
Color	Beige
Interface Feature, front	Two wire terminals (2)   fiber Duplex (2)
Mounting	Surface
Outlet Orientation	Flat
Port Marking Type	Label
Total Ports, quantity	4
Dimensions	
Height	38 mm   1.496 in
Width	142.3 mm   5.602 in
Depth	116.2 mm   4.575 in

### **Electrical Specifications**

Input Power	100 W (NEC Class 2)	
Input Voltage	30 Vac   60 Vdc	
Electrical Safety Standard	CB   IEC 60950-1   IEC 62368-1   UL   cUL	
Matacial Cascifications		

#### Material Specifications

Material Type Polycarbonate

### **Environmental Specifications**

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 16, 2023



# 760249095

Environmental Space	Indoor
Flammability Rating	UL 94 V-0

## Packaging and Weights

Packaging quantity	1
Weight, net	0.149 kg   0.328 lb

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 16, 2023

