

P421004-560-1

CF141 Jumper with interface types NEX10 Male and NEX10 Female,
0.56 m



Product Classification

Product Type	Braided cable assembly
Product Series	CF141-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CF141-50
Interface, Connector A	NEX10 Male
Interface, Connector B	NEX10 Female
Specification Sheet Revision Level	A

Dimensions

Length	0.56 m 1.837 ft
Nominal Size	0.141 in

Electrical Specifications

3rd Order IMD	-117 dBm
3rd Order IMD Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
100–3000 MHz	1.135	24

Jumper Assembly Sample Label

Batch Manufacturing Date (two digit year and week)

Manufacturing Plant Product Revision

0123456789 US22 1240 /A

COMMScope[®] Andrew Solutions[™]

F4-DMDM-2M-D — Part Number

2 M (6.562 FT)
SUREFLEX ASSEMBLY
U.S. PATENT 5802710

Product of UNITED STATES

12US220001242 — Serial Number

