FGS-FLEXV-C



FiberGuide® FlexVertical Trough, 2x2in, Yellow

Product Classification

Asia Australia/New Zealand EMEA Latin America North America
CommScope®
Drop kit
FiberGuide®
FGS

General Specifications

Product Feature	Snap-together design
Angle/Bend Direction	30°
Color	Yellow
Orientation	Vertical
Section Type	Vertical section
Dimensions	

Height	76.2 mm 3 in
Width	64.516 mm 2.54 in
Length	67.056 mm 2.64 in
System Dimensions	51 mm x 51 mm (2 in x 2 in)

Material Specifications

 Material Type
 Engineering Thermoplastic

Environmental Specifications

Flammability Rating	CSA S143 UL 2024 UL 94 V-0
Halogen Characteristics	Blue Angel TCO '99 WEEE
Safety Standard	CSA UL

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 18, 2023



FGS-FLEXV-C

Packaging and Weights

Included	Hardware
Packaging quantity	1
Weight, net	0.027 kg 0.06 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 18, 2023

