

# XP-2025

---



Crossover Plate, joins 2-3/8 in to 2-7/8 in OD round members

## Product Classification

**Product Type** Clamp plate

## General Specifications

**Mounting** Crossover plate

## Dimensions

**Mounting Diameter, maximum** 73.025 mm | 2.875 in

**Mounting Diameter, minimum** 60.325 mm | 2.375 in

**Material Thickness** 9.525 mm | 0.375 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Environmental Specifications

**EPA with 1/2 in (12 mm) radial ice** ft<sup>2</sup>

## Packaging and Weights

**Included** Plates | U-bolts

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



# XP-2025

---

## \* Footnotes

**EPA with 1/2 in (12 mm) radial ice** EPA—Effective Projected Area