

FJ-2S-1-LC

HELIAX® Direct tail, 2 single mode fiber, 6 mm cable, outdoor fiber IP-LC connectors at RRU, 2 LC connectors end 2



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Wireless Fiber Cable Assemblies
Product Brand	HELIAX®
Product Series	FJ
Ordering Note	CommScope® non-standard product

General Specifications


Construction Type	Direct fiber tail
Interface, Connector A	IP-LC
Interface Feature, connector A	Outdoor
Interface Body Style, connector A	Straight
Interface, Connector B	LC/UPC
Interface Feature, connector B	Outdoor
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	2

Dimensions

Cable Assembly Length Range (m)	2 – 50
Diameter Over Jacket	6 mm 0.236 in

Ordering Tree

FJ-2S-1-LC-10M



Mechanical Specifications

Minimum Bend Radius 60 mm | 2.362 in

Optical Specifications

Fiber Type G.657.A2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.5

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Environmental Space Outdoor

Packaging and Weights

Cable weight 24.9 kg/km | 16.732 lb/kft

FJ-2S-1-LC

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification

Designed, manufactured and/or distributed under this quality management system

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)