

FGSB-MIDY

Base Product



FiberGuide® 2in Flex Tube, Slotted, Black

- Engineers and installers can benefit from the large suite of available FiberGuide design tools
- FiberGuide is an optical raceway system for central office, mobile switching center and data center applications
- FiberGuide maintains a minimum bend radius throughout the entire system, regardless the system size
- FiberGuide products are designed and manufactured to ensure total off-frame fiber cable protection

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Convoluted tube
Product Brand	FiberGuide®
Product Series	FGSB

General Specifications


Color	Black
Orientation	Vertical
Section Type	Vertical section

Dimensions

Tube Length Range (ft)	5 – 350
Tube Outer Diameter	50.8 mm 2 in

Ordering Tree

FGSB-MIDY



Tube Color

9	empty	yellow
	B	black

Tube Length, examples

11	5F	5 feet
	350F	350 feet

Tube Type

10	MIDY	Slotted flexible tube, 2 in diameter
	MFTY	Slotted flexible tube, 7/8 in diameter
	MISY	Solid flexible tube, 2 in diameter
	MLDY	Slotted flexible tube, 1 in diameter

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

