

# PTS1P-NMQR-4M

---

PTS1-50-P SureFlex® Jumper with interface types N Male and QMA Male Right angle, 4 m



## Product Classification

<b>Product Type</b>	Cable assembly, plenum
<b>Product Series</b>	PTS1-50-P

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Right angle
<b>Interface, Connector A</b>	N Male
<b>Interface, Connector B</b>	QMA Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	4 m   13.123 ft
<b>Nominal Size</b>	1/4 in

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
<b>700–3000 MHz</b>	1.433	15

## Jumper Assembly Sample Label

# PTS1P-NMQR-4M

---



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition