



Ultra Low Loss (ULL) Multimode OM5 MPO12 (Pinned) to Unconnectorized, Armored Pre-terminated Trunk Cable, 36-Fiber, Plenum

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   Europe   Latin America   Middle East /Africa   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber trunk cable assembly
<b>Product Brand</b>	SYSTIMAX ULL
<b>Ordering Note</b>	For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration

## General Specifications

<b>Color, boot A</b>	Black
<b>Color, boot B</b>	Black
<b>Color, connector A</b>	Lime green
<b>Color, connector B</b>	Lime green
<b>Connector A, quantity</b>	3
<b>Connector B, quantity</b>	0
<b>Construction Type</b>	Armored   Stranded
<b>Fibers per Subunit, quantity</b>	12
<b>Furcation Color</b>	Lime green
<b>Interface, Connector A</b>	MPO-12/UPC Male
<b>Interface Feature, connector A</b>	Pinned
<b>Interface, Connector B</b>	Unterminated
<b>Jacket Color</b>	Lime green
<b>Polarity</b>	Method B Enhanced (ULL)
<b>Total Fibers, quantity</b>	36

## Dimensions

# UHVVMXUCAG

---

<b>Breakout Length</b>	33 in
<b>Cable Assembly Length Range (m)</b>	3 – 999
<b>Cable Assembly Length Range (ft)</b>	10 – 999

## Mechanical Specifications

<b>Cable Retention Strength, maximum</b>	11.24 lb @ 0 °   4.40 lb @ 90 °
--	---------------------------------

## Optical Specifications

<b>Fiber Mode</b>	Multimode   Multimode
<b>Fiber Type</b>	OM5, LazrSPEED®

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Environmental Space</b>	Indoor   Plenum

## Included Products

- |                                |   |   |
|--------------------------------|---|---|
| 760230227<br>P-036-MZ-5G-F12LM | - | LazrSPEED® Plenum MPO Trunk Cable, interlocking aluminum armored with plenum jacket, 36 fiber multi-unit with 12 fiber subunits |
| 860617240                      | - | MPO12, ULTRA LOW LOSS, MALE, OM5, LIME, 3mm   |