

F1A-HMQR-12M

FSJ1-50A SureFlex® Jumper with interface types 4.3-10 Male and QMA Male Right angle, 12M



- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	Wireless transmission cable assembly
Product Series	FSJ1-50A

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Interface, Connector A	4.3-10 Male
Interface, Connector B	QMA Male
Specification Sheet Revision Level	A

Dimensions

Length	12 m 39.37 ft
Nominal Size	1/4 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.433	15

Jumper Assembly Sample Label

F1A-HMQR-12M



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Included Products

- F1HM-S2 – 4.3-10 Male for 1/4 in foam coaxial cable, factory attached
- F1TQMR-SX – QMA Male Right Angle for 1/4 in foam and air coaxial cable, factory attached
- FSJ1-50A – FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket