CMAX-LHM2-22-153



Low PIM Directional High Capacity Venue MIMO Antenna 4G/5G/C-Band, 617–960 MHz, 1695–2700 MHz and 3300-4200 MHz, 22-Deg

Product Classification

Product Type Over-the-head stadium antenna

General Specifications

ApplicationIndoor/OutdoorAntenna TypeDirectionalAntenna Array CharacteristicMIMO 2x2

 $\textbf{Polarization} \hspace{2cm} \pm 45^{\circ}$

Color White (RAL 9016)

Number of Ports

Radome Material PVC, UV resistant **RF Connector Interface** 4.3-10 Female

Dimensions

 Width
 417 mm | 16.417 in

 Depth
 140 mm | 5.512 in

 Length
 1150 mm | 45.276 in

Electrical Specifications

Impedance50 ohmLightning Protectiondc Ground

Operating Frequency Band 1695 – 2200 MHz | 2200 – 2700 MHz | 3300 – 4200 MHz | 617 – 806 MHz | 806

- 960 MHz

Electrical Note Values typical, unless otherwise stated

Electrical Specifications

 Frequency Band, MHz
 617–806
 806–960
 1695–2200
 2200–2700
 3300–4200

 Gain, dBi
 11.8
 12.5
 10.8
 11.7
 11.2

Page 1 of 2



CMAX-LHM2-22-153

Beamwidth, Horizontal, degrees	24	19	27	21	24
Beamwidth, Vertical, degrees	76	73	75	67	74
Horizontal Sidelobe, dB	14	14	15	15	15
Front-to-Back Ratio, Copolarization 180° ± 30°, dB	20	20	20	20	20
CPR at Boresight, dB	19	20	16	17	18
Isolation, Cross Polarization, dB	22	25	25	25	25
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-153
Input Power per Port, maximum, watts	200	200	200	200	200

Mechanical Specifications

Wind Loading @ Velocity, maximum 1,557.0 N @ 241 km/h (350.0 lbf @ 150 mph)

Wind Speed, maximum 241.4 km/h (150 mph)

Environmental Specifications

Operating Temperature $-40 \, ^{\circ}\text{C} \text{ to } +60 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F to } +140 \, ^{\circ}\text{F})$

Relative Humidity Up to 100%

Ingress Protection Test Method IEC 60529:2001, IP65

Vibration Test Method ASTM D4169 | IEC 60068-2-6

Packaging and Weights

 Width, packed
 480 mm | 18.898 in

 Depth, packed
 240 mm | 9.449 in

 Length, packed
 1300 mm | 51.181 in

IncludedMounting bracketNet Weight, with mounting kit13.8 kg | 30.424 lb

Packaging quantity 1

 Weight, gross
 17.5 kg | 38.581 lb

 Weight, net
 11 kg | 24.251 lb

