1RU-SP1164001 | 1RU SPLTR PNL 1X64 APC/LC



1RU panel, 1X64 split ratio, 1 splitter, LC/APC connectors

• *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	Asia Australia/New Zealand China EMEA India Latin America North America
Product Type	Splitter patch panel
Product Series	1RU
Government Funding	Build America Buy America (BABA) compliant*
General Specifications	
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Distribution Type	1 x 64 splitter
Interface, Input	LC/APC
Interface, Output	LC/APC
Splitter, quantity	1
Dimensions	
Height	43.69 mm 1.72 in
Width	482.6 mm 19 in
Length	199.89 mm 7.87 in
Optical Specifications	
Directivity, minimum	55 dB
Polarization Dependent Loss, maximum	0.4 dB
Uniformity, maximum	2.3 dB
Wavelength Range	1260-1650 nm
Insertion Loss, Splitter, maximum	21 dB

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 11, 2024



1RU-SP1164001 | 1RU SPLTR PNL 1X64 APC/LC

50 dB Return Loss, Splitter, minimum **Environmental Specifications Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F) **Relative Humidity** 5%-95%, non-condensing Packaging and Weights Packaging quantity 1 Regulatory Compliance/Certifications Classification Agency CHINA-ROHS Below maximum concentration value **REACH-SVHC** Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

UK-ROHS

ROHS

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 11, 2024

