

# RT-NF7-2-126

---



High Capacity Non-Penetrating Roof Frame, 7 ft face, two 2-7/8 in OD x 126 in pipes

## Product Classification

<b>Product Type</b>	Non-penetrating roof frame
<b>Ordering Note</b>	NSTD445 Compliant

## General Specifications

<b>Mounting</b>	Non-penetrating
<b>Pipe, quantity</b>	2

## Dimensions

<b>Height</b>	3,200.4 mm   126 in
<b>Face Width</b>	2,286 mm   7.5 ft
<b>Width</b>	2,286 mm   90 in
<b>Length</b>	2,377 mm   7.8 ft
<b>Pipe Length</b>	3,200.4 mm   126 in
<b>Face Support Pipe Diameter</b>	73.152 mm   2.88 in
<b>Pipe Outer Diameter</b>	73.152 mm   2.88 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Mechanical Specifications

<b>Wind Rating Test Method</b>	TIA/EIA-222
--------------------------------	-------------

## Packaging and Weights

<b>Included</b>	Ballast tray   Frame   Plain end pipes
-----------------	--