
# UJXQZUCTH

#### **Base Product**



Ultra Low Loss (ULL) OM4 MPO APC (Pinned) to Unconnectorized, Fiber Trunk Cable Assembly, 48-Fiber, Dual Rated (OFNR/LSZH)

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

### General Specifications

Connector A, quantity 6

Color, boot AGrayColor, connector AGreenConnector B, quantity0

Construction Type Stranded

Furcation Color Agua

Interface, Connector A MPO-08/APC Male

Interface, Connector B Unterminated

Jacket Color Aqua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 48

Dimensions

Breakout Length 22 in

Cable Assembly Length Range (m) 3 - 305


Cable Assembly Length Range (ft) 10 - 999

Page 1 of 3



# UJXQZUCTH

### Ordering Tree



#### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0  $^{\circ}$  | 4.40 lb @ 90  $^{\circ}$ 

Optical Specifications

Fiber Mode Multimode

**Fiber Type** OM4, LazrSPEED®

### **Environmental Specifications**

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Dual Rated LSZH/Riser | Indoor

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



**COMMSCOPE®** 

# UJXQZUCTH

#### Included Products

760248166 N-048-MP-5K-F08AQ/20T/D

- Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 48 fiber multi-unit with 8 fiber 2.0mm subunits, Gel-free, Multimode OM4, Feet jacket marking, Aqua jacket color, Dca flame rating
- 860662230 MPO8,ULL,Multimode,MALE,APC,GREEN,2 mm

