

LSX-LM0000

LSX Fiber Term Panel 8 Ru, 288 - LC/APC, Adapter Only



Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	LGX

General Specifications

Functionality	Patching
Application	Used in LSX-style frames only
Color	Putty white
Color, front	White
Growth Configuration	Fully loaded
Interface, front	LC/APC
Rack Type	EIA 23 in
Rack Units	8
Shelf Movement	Fixed
Total Ports, quantity	288

Dimensions

Height	279 mm 10.984 in
Width	533.4 mm 21 in
Depth	279 mm 10.984 in

Material Specifications

Finish	Powder coated
---------------	---------------

LSX-LM0000

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

