FDT-CK348NXA0000



iFDT Indoor Fiber Distribution Terminal, 48-fiber, LC/UPC, soft-wall pigtails, mechanical splice trays, no cable

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

Product Classification

Regional Availability North America

Fiber distribution terminal **Product Type**

Product Series IFDT

General Specifications

Adapters, quantity 24

Cable Entry Location Bottom right | Top right

Cable Type Pigtails - Stranded

Color Putty white

Front Door Type Double hinged

Growth Configuration Fully loaded

Interface LC/UPC

Lock Type Padlock ready

Mounting Wall

Port, quantity 48

Splice Tray Chip Type Heat shrink

Splicing Capacity, maximum 48

Dimensions


Height 476.25 mm | 18.75 in Width 368.3 mm | 14.5 in 127 mm | 5 in

Depth

Ordering Tree



FDT-CK348NXA0000



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA, Type 12 | Telcordia GR-2898-CORE

Packaging and Weights

Packaging quantity



FDT-CK348NXA0000

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

