

760253632 | KJ-C6-BK



KJ-Series Modular Jack, RJ45, Cat6 Unshielded, Black

Alternative products available:

2291216-2
KJ610-BK

KJ-Series Modular Jack, RJ45, Cat6 Unshielded, Black

Product Classification

Regional Availability	Asia Australia/New Zealand
Portfolio	NETCONNECT®
Product Type	Modular jack
Product Series	KJ Series

General Specifications

ANSI/TIA Category	6
Application	For use with the CPP-UMOD-KJ-1U-24 panel 760254673
Cable Type	Unshielded
Color	Black
Conductor Type	Solid Stranded
Integrated Dust Cover Type	None
Mounting Note	Color matches with KJ-style Black Faceplates and Surface Mount Boxes
Outlet Type	Keystone
Termination Tool	110 Punchdown tool
Termination Type	IDC
Transmission Standards	ANSI/TIA-568.2-D ISO/IEC 11801 Class E
Wiring	T568A T568B

Dimensions

Panel Cutout, recommended	14.79 x 19.31 mm (0.58 x 0.76 in)
Panel Thickness, recommended	1.6 mm 0.063 in

760253632 | KJ-C6-BK

Height	16.3 mm 0.642 in
Width	16.9 mm 0.665 in
Depth	30 mm 1.181 in
Contact Plating Thickness	1.27 µm
Compatible Conductor Gauge, solid	26–22 AWG
Compatible Conductor Gauge, stranded	26–22 AWG

Electrical Specifications

Remote Powering	Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002
PoE Durability	Supports IEEE 802.3bt Type 4 (90 W) applications greater than 3000 plug to jack mating cycles

Material Specifications

Contact Base Material	Phosphor Bronze
Contact Plating Material	Gold
Material Type	Polycarbonate

Mechanical Specifications

Plug to Jack Mating Cycles	Complies to IEC 60603-7 series
-----------------------------------	--------------------------------

Environmental Specifications

Flammability Rating	UL 94 V-0
----------------------------	-----------

Packaging and Weights

Packaging quantity	24
Packaging Type	Bag

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

