

# 760253735 | PPL-DM-12U-12LC-OM5-SAMPLE



Propel Sample Multimode OM5 MPO-12 Distribution Module, 6 duplex LC to 1X12f MPO, No fiber

- Can be installed and removed from front or rear of panel
- This component requires 3 of the 12 lanes on the Propel Panel blade

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Breakout module
<b>Product Brand</b>	Propel
<b>Product Series</b>	PPL

## General Specifications

<b>Functionality</b>	Breakout
<b>Color, front</b>	Lime green
<b>Color, rear</b>	Gray
<b>Interface, front</b>	LC/UPC
<b>Interface Feature, front</b>	Internal shutters
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	Internal shutters
<b>Total Fibers, quantity</b>	0
<b>Total Ports, quantity, front</b>	6
<b>Total Ports, quantity, rear</b>	1

## Dimensions

<b>Height</b>	11 mm   0.433 in
<b>Width</b>	98 mm   3.858 in
<b>Depth</b>	170 mm   6.693 in

## Optical Specifications

<b>Insertion Loss, maximum</b>	dB
--------------------------------	----

## Environmental Specifications

**Safety Standard** UL 62368

## Packaging and Weights

**Packaging quantity** 1