

L4A-NMNR-P

LDF4-50A SureFlex® Jumper with interface types N Male and N Male Right Angle



Product Classification

Product Type	SureFlex® Premium, static PIM
Product Brand	HELIAX® SureFlex®

General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Straight
Body Style, Connector B	Right angle
Interface, Connector A	N Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A

Dimensions

Cable Assembly Length Range (ft)	1 – 100
Nominal Size	1/2 in

Electrical Specifications

3rd Order IMD Static	-112 dBm
3rd Order IMD Static Test Method	Two +43 dBm carriers per IEC 62037
DTF, Connector A	-34 dB
DTF, Connector B	-34 dB

Jumper Assembly Sample Label

L4A-NMNR-P



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition