CAF-6C6C-LSOM



Armored Jumper G657.A2 SC/APC to SC/APC Simplex, 3.0mm LSZH, Yellow

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | India | North America

Portfolio CommScope®

Product Type Fiber patch cord, simplex

Product Series CAF

General Specifications

Connector A, quantity 1

Color, boot A Green
Color, connector A Green

Connector B, quantity 1

 Color, boot B
 Green

 Color, connector B
 Green

 Construction Type
 Armored

 Interface, Connector A
 SC/APC

 Interface, Connector B
 SC/APC

 Jacket Color
 Yellow

Total Fibers, quantity 1

Dimensions

Cable Assembly Length Range (m) 1 - 300

Cable Assembly Length Range (ft) 3 - 999

Diameter Over Jacket 3 mm | 0.118 in

Mechanical Specifications

Tensile Load, long term, maximum100 N | 22.481 lbfTensile Load, short term, maximum200 N | 44.962 lbf

COMMSC PE°

CAF-6C6C-LSOM

Cable Retention Strength, maximum 15.43 lb @ 0°

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2, TeraSPEED®

Insertion Loss, maximum0.25 dBReturn Loss, minimum60 dB

Environmental Specifications

Operating Temperature -25 °C to +70 °C (-13 °F to +158 °F)

Environmental Space Low Smoke Zero Halogen (LSZH)

Qualification Standards IEC 61753-1, category OP

Packaging and Weights

Packaging quantity 1