

# 7845389-1034 | UAP2 80-85/17E/19/37T F-DC



Carrier Access Point with MIMO 2x2 Radio Module for Low Power SMR 800, CEL 850, AWS 1700, PCS 1900 and C-Band Applications, Fiber fed, DC

## Product Classification

<b>Product Type</b>	Access point
<b>Product Brand</b>	ERA®
<b>Product Series</b>	UAP2

## General Specifications

<b>Antenna Type</b>	MIMO Antenna
<b>Fan Kit</b>	Included
<b>Fed Type</b>	Fiber fed
<b>Note</b>	Detailed Product Specifications are available. Please contact your local CommScope representative.
<b>Power Class</b>	Low
<b>Powering Type</b>	External DC powered

## Electrical Specifications

<b>License Band</b>	AWS 1700   C-Band   CEL 850   PCS 1900   SMR 800
<b>Voltage Range</b>	-57 to -42 Vdc

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

