

MTC9076M69M96



T-Arm Monopole Mount, Includes Ring Mount for 15"-50" OD Monopole, 6.5 ft face plus (9) 2-7/8" OD x 96" Antenna Pipes and Corner Tiebacks

Product Classification

Product Type Monopole T-frame kit

General Specifications

Mounting Monopole, 381–1270 mm (15–50 in) OD

Pipe, quantity 9

Sectors, quantity 3

Dimensions

Height 2,438.4 mm | 96 in

Face Width 1.981 m | 6.5 ft

Width 2,133.6 mm | 84 in

Pipe Length 2,438.4 mm | 96 in

Mounting Diameter, maximum 1270 mm | 50 in

Mounting Diameter, minimum 381 mm | 15 in

Pipe Outer Diameter 73.025 mm | 2.875 in

Stand-off Distance 1,010.412 mm | 39.78 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Wind Rating Test Method TIA/EIA-222-G

Packaging and Weights

Included Pipe mounts | Plain end pipes | Ring mount | Stand-off arms

Packaging quantity 1

MTC9076M69M96

Weight, net 574.702 kg | 1267 lb

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code