



HTB2 Home Termination Box with Patch capacity for 1 SC/UPC connection and splice capacity up to 4 splices, SC/UPC Adapter included, no pigtails included

- SC/UPC, SC/APC, LC/UPC and LC/APC connector versions

Product Classification

Regional Availability	India Latin America
Product Type	Fiber wall outlet
Product Series	HTB2

General Specifications

Adapters, quantity	1
Cable Ports, quantity	7
Color	White
Distribution Type	1 port
Front Cover Type	Screw-on
Interface Type	SC/UPC
Lock Type	Standard screw
Mounting	Wall mount
Patching Capacity, maximum	2
Pigtails Included, quantity	0
Port, quantity	1
Splicing Capacity, maximum	4

Dimensions

Height	86 mm 3.386 in
Width	86 mm 3.386 in
Depth	22 mm 0.866 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS)
----------------------	---------------------------------------

Environmental Specifications

Operating Temperature	-5 °C to +55 °C (+23 °F to +131 °F)
Environmental Space	Indoor
Flammability Rating	UL 94 V-0
Qualification Standards	IEC 60529, IP40

Packaging and Weights

Packaging Type	Box
Weight, net	0.05 kg 0.11 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

