


760254720



MSO All-In-One FLX-PON Cabinet, 144F, LC/APC, LGX Splitters, Dry Single Armored Loose Tube, 100 ft, 1x 144F Distribution Cables, 1x 24F Feeder Cable

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber distribution hub
Product Brand	CommScope FLX™
Product Series	FLX
Warranty	Two years

General Specifications

Access	Front Rear Side
Acoustic Level, maximum	60 dB
Alarm Type	Door alarm
Auxiliary Power Input	Yes
Cable Type	Armored - Single Loose Tube
Color	Light Gray (RAL 7035)
Distribution Cables, quantity	1
Distribution Ports, quantity	144
Fibers per Distribution Cable, quantity	144
Fibers per Feeder Cable, quantity	24
Interior LED light	Both chambers
Interface, Input	LC
Interface Feature, Input	APC
Mounting	Handhole Pad
Node Storage Capacity	2
Rack Storage	13RU (19 in)
Split Ratio	Symmetrical

760254720

Splitter Slots, quantity	12
Splitter Type	1 x 64
Splitter, quantity	2
Heat Management	1,500 W Thermosiphon

Dimensions

Height	1216 mm 47.874 in
Width	1224 mm 48.189 in
Depth	697 mm 27.441 in
Cable Length	30.48 m 100 ft
Enclosure Size	Large

Material Specifications

Finish	Powder coated
Material Type	Aluminum

Environmental Specifications

Environmental Space	Above ground
Qualification Standards	Telcordia GR-487-CORE

Packaging and Weights

Packaging quantity	1
Packaging Type	Pallet
Weight, net	147.418 kg 325 lb
Weight, without cable	122.924 kg 271 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

760254720

Warranty

For more information, please consult our Product Warranty guidelines