

760253637 | OUT-OUT-FP-G



Outdoor Outlet Cover, single gang, universal, two ports,gray

Product Classification

Regional Availability	Asia EMEA Latin America North America
Portfolio	CommScope®
Product Type	Box

General Specifications

Application	Used with KJ Series outlets with adapter Used with M Series modular information outlet Used with SL Series outlets
Color	Gray
Outlet Orientation	Angled
Port Marking Type	Label
Total Ports, quantity	2

Dimensions

Height	150 mm 5.906 in
Width	95.6 mm 3.764 in
Depth	55 mm 2.165 in

Material Specifications

Material Type	Flame/UV-resistant plastic for enclosure and cover
----------------------	----------------------------------------------------

Environmental Specifications

Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Environmental Space	Indoor/Outdoor
Qualification Standards	IEC 60529, IP67

Packaging and Weights

760253637 | OUT-OUT-FP-G

Packaging quantity	1
Packaging Type	Box
Weight, net	0.28 kg 0.617 lb