

F2P43-HMHM-3M

FSJ2-50 SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male, 3 m



Product Classification

Product Type	Wireless transmission cable assembly
Product Brand	HELIAX® SureFlex®
Product Series	FSJ2-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

Dimensions

Length	3 m 9.843 ft
Nominal Size	3/8 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
680–806 MHz	1.15	23.13
806–960 MHz	1.13	24.29
1427–1535 MHz	1.13	24.29
1700–2300 MHz	1.15	23.13
2535–2655 MHz	1.25	19.08
3400–4100 MHz	1.25	19.08
4400–5000 MHz	1.25	19.08

F2P43-HMHM-3M

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition