A7801367 | SFP+, 10GBase CWDM-610, up to 40 km, TAA



Small form factor pluggable+ Module, 10G BASE, CWDM, Singlemode, TAA compliant

• Trade Agreements Act (TAA) compliant

Product Classification

Product Type Optical module

Product Series SFP+

General Specifications

Interface LC/UPC

Note Detailed Product Specifications are available. Please contact your local

CommScope representative.

Dimensions

 Height
 12 mm | 0.472 in

 Width
 14 mm | 0.551 in

 Depth
 57 mm | 2.244 in

Optical Specifications

Fiber Type 9/125 μm, singlemode

Average Optical Output Power, maximum 4 dBm

Average Optical Output Power, minimum -1 dBm

Rx/Tx Power Accuracy ±3dB / ±3dB

Operating Wavelength 1260 – 1620 nm (Rx) | 1611 nm

Receiver Sensitivity at Bandwidth Range -15.8 dBm @ 9.95-10.5 Gb/s

Receiver Overload -1 dBm

Environmental Specifications

Operating Temperature 0 °C to +70 °C (+32 °F to +158 °F)

Page 1 of 2

A7801367 | SFP+, 10GBase CWDM-610, up to 40 km, TAA

Packaging and Weights

 Height, packed
 20 mm | 0.787 in

 Width, packed
 105 mm | 4.134 in

 Depth, packed
 65 mm | 2.559 in

Packaging quantity 1

Packaging Type Box

 Weight, gross
 0.036 kg | 0.079 lb

 Weight, net
 0.022 kg | 0.049 lb