MPW-MNN2SXXXM-EF

Ultra Low Loss (ULL) Singlemode G.657.A2, 2X3, MPO12 (Non-Pinned) to MPO12 (Non-Pinned), 24-Fiber, Conversion Array, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber conversion array cable assembly

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary

based on cable configuration

General Specifications

Connector A, quantity 2

Color, boot A Red

Color, connector A Green

Connector B, quantity 3

Color, boot B Black

Color, connector B Green

Construction Type Stranded

Furcation Color Yellow

Interface, Connector A MPO-12/APC Female

Interface, Connector B MPO-12/APC Female

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Total Fibers, quantity 24

Dimensions

Breakout Length 12 in | 24 in | 36 in | 48 in | 60 in | 72 in

Cable Assembly Length Range (m) 3 - 305

Cable Assembly Length Range (ft) 10 - 999

Optical Specifications

Fiber Mode Singlemode

COMMSCOPE®

MPW-MNN2SXXXM-EF

Fiber Type G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 °F to +140 °F)}$

Environmental Space Indoor | Plenum

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

760237965 – Fiber indoor cable, Plenum for MPO Trunks, 24 fiber with 12 fiber subunits, Singlemode G.657.

P-024-MP-8G1-F12YL A2/B2, Feet jacket marking, Yellow jacket color

860637706 – MPO8, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm 860638318 – MPO12, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm

