

# RR-FA4



RRU Mount Kit for Back-to-Back Mounting of (2) RRUs on up to 5.6" Round, 6" 60 degree or 4.5" 90 Degree Angle

Accommodates a wide variety of radios from all manufacturers.

Features integrated lifting points for safe and efficient hoisting of radios to the mounting location

Supports all typical RRH units from Ericsson, Nokia, Samsung, Huawei, Fujitsu

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Remote radio head unit mount
<b>Ordering Note</b>	CommScope® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Mounting</b>	Round and angle legs
<b>Radio Compatibility, Ericsson</b>	(2) RRUS11/12/32, 2212, 4415, 4426, 4478   4426   4435   4449   4455   4467   4478   4480   4490   4890   8843   8863
<b>Radio Compatibility Samsung</b>	RF4440D   RF4442D   RFV01U-D1A   RFV01U-D2A   RT2201-46A   RT4401-48A   RT8808-77A
<b>Tower Taper</b>	Non-tapered   Tapered

## Dimensions

<b>Height</b>	408.94 mm   16.1 in
<b>Width</b>	237.998 mm   9.37 in
<b>Length</b>	372.618 mm   14.67 in
<b>Mounting Diameter 2, maximum</b>	152.4 mm   6 in
<b>Mounting Diameter 2, minimum</b>	38.1 mm   1.5 in
<b>Mounting Diameter, maximum</b>	142.24 mm   5.6 in
<b>Mounting Diameter, minimum</b>	60.96 mm   2.4 in

# RR-FA4

---

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Clamps | Hardware

**Packaging quantity** 2

**Weight, net** 16.03 kg | 35.34 lb

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant



## \* Footnotes

### Warranty

For more information, please consult our Product Warranty guidelines