A 3.0 MANUFACTURING/SPECIAL RE U-BOLTS USING TURN- EQUAL FORCE ON EAC 4.0 TEST 5.0 PACKAGING 5.1 PACKAGING SHALL ME 5.2 PRINTED DOCUMENT T	MER REQUIREMENTS EQUIREMENTS ECURING FLAT PLATES BY THE TURN-OF-NUT ME OF-NUT METHOD WITH ATTENTION TO LEAVE EQ	UAL DISTANCE AN	ND	6 7	8	9 10 11 12 REVISIONS REV. DESCRIPTION DATE APPROVED A INITIAL RELEASE JL1183 01SEP22 VICENTE 40155958CMO A
В					FITS UP TO Ø11 (NOT INCLUDED	4.3[4.50] O.D. PIPE IN THIS KIT)
С			2			C
					\int	
D						
E			3		FITS UF (NOT IN	P TO Ø88.9[3.50] O.D. PIPE NCLUDED IN THIS KIT)
			4			
F						F
						COMMSCOPE, INC. OF NORTH CAROLINA
	PROVIDED FOR ASSEMBLY PURPOSES;					TOLERANCES SAP MATERIAL MASTER 0 PLACE X[.X] ± 6[0.25] 2 PLACE.XX[.XXX] ± 1.50[0.06] 1 PLACE .X[.XX] ± 3.0[0.12] ANGLES ± 2°
	Y BE SHIPPED AS PARTS WITHIN AN INCL				DENSITY 0.29 lbs/in ³	GALV A123 GALV A123
ITEM NO. PART NO. 1 P574-029-01	DESCRIPTION BENT PLATE BRACKET	QTY.	NOTE NO.		MASS 29.84 lbs	
2 VCP	CLAMP, MOUNTING	4			VOLUME 105.34 in³ SURFACE AREA 669.16 in²	CE JL1183 01SEP22 UNIVERSAL CHANNEL CROSSOVER
3 GB-05605FT	5/8" X 6" GALV BOLT KIT FULL THREAD	8	INCLUDED BOLT, LOCK WASHER AND NUT		DENSITY 0.0079 g/mm	
4 GWF05A	GALV FLAT WASHER HARDENED 5/8", 1.30D	8			MASS 13562.5666 grams VOLUME 1726397.2704 mm	AD VCORTEZ1 09/14/2022 n³ ВЗВЕ RE JL1183 09/15/2022 VCORTEZ1 09/15/2022 SCALE DOCUMENT NO.
					SURFACE AREA 431713.5962 mm HEIGHT 279[11.0]	
				C 2022 CommScope, Inc. Confidential	LENGTH 295[11.6]	Additive of the second status and the second
1	2 3	4	5	6 7	8	9 10 11 12