

# 7844068-02 | WCS-4 DC



ERA® Wireless Communications Switch Subrack, 4 U -48Vdc, with integrated DCDC converter

This unit does not support CAT6A powered access points.

## Product Classification

**Product Type** Subrack

**Product Brand** ERA®

## General Specifications

**Mounting** Rack

**Note** Detailed Product Specifications are available. Please contact your local ANDREW representative.

**Rack Type** EIA 19 in

**Slots Available, quantity** 19

## Dimensions

**Height** 177 mm | 6.969 in

**Width** 482 mm | 18.976 in

**Depth** 450 mm | 17.717 in

## Packaging and Weights

**Height, packed** 540 mm | 21.26 in

**Width, packed** 600 mm | 23.622 in

**Depth, packed** 290 mm | 11.417 in

**Included** Fan filter | Fan tray

**Weight, gross** 15.8 kg | 34.833 lb

**Weight, net** 13.4 kg | 29.542 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value

# 7844068-02 | WCS-4 DC

---

ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted

