

# 760255697 | RMM-12AUR-12AUF-SM-ULL



1RU rack mounted Singlemode mesh module with 24, MPO12 inputs on the back from separate network enclaves and 24, MPO12 outputs to the desk top on the front with Ultra-Low Loss (ULL) performance

## Product Classification

<b>Regional Availability</b>	Asia   EMEA   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel

## General Specifications

<b>Interface, front</b>	MPO
<b>Interface Feature, front</b>	Shuttered   Unpinned
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	Shuttered   Unpinned
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Fixed
<b>Total Fibers, quantity</b>	288
<b>Total Ports, quantity</b>	48
<b>Total Ports, quantity, front</b>	24

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	OS2

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

# 760255697 | RMM-12AUR-12AUF-SM-ULL

---

CHINA-ROHS

Above maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

