


# U4VQXLUTN

## Base Product



Ultra Low Loss ULL OM5 MPO8 UPC pinned to LC/UPC Uniboot Ruggedized fanout Cable, 192-Fiber, LSZH, 8 fiber PmP 2.0 mm /B2ca

## Product Classification

|                              |  |
|------------------------------|--|
| <b>Regional Availability</b> | Europe   |
| <b>Portfolio</b>             | CommScope®   |
| <b>Product Type</b>          | Ruggedized fanout  |
| <b>Product Brand</b>         | Propel   SYSTIMAX ULL  |
| <b>Ordering Note</b>         | For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration |

## General Specifications

|                                       |                         |
|---------------------------------------|-------------------------|
| <b>Connector A, quantity</b>          | 24                      |
| <b>Color, boot A</b>                  | Gray                    |
| <b>Color, connector A</b>             | Lime green              |
| <b>Connector B, quantity</b>          | 192                     |
| <b>Color, boot B</b>                  | Lime green              |
| <b>Color, connector B</b>             | Black                   |
| <b>Construction Type</b>              | Stranded                |
| <b>Furcation Color</b>                | Lime green              |
| <b>Interface, Connector A</b>         | MPO-08/UPC Male         |
| <b>Interface, Connector B</b>         | LC/UPC                  |
| <b>Interface Feature, connector B</b> | Uniboot                 |
| <b>Jacket Color</b>                   | Lime green              |
| <b>Polarity</b>                       | Method B Enhanced (ULL) |
| <b>Fibers per Subunit, quantity</b>   | 8                       |
| <b>Total Fibers, quantity</b>         | 192                     |

# U4VQXLUTN

## Dimensions

|   |          |
|---|----------|
| <b>Breakout Length</b>                  | 22 in    |
| <b>Cable Assembly Length Range (m)</b>  | 3 – 305  |
| <b>Cable Assembly Length Range (ft)</b> | 10 – 999 |

## Ordering Tree



## Mechanical Specifications

|  |                                 |
|--|---------------------------------|
| <b>Cable Retention Strength, maximum</b> | 11.24 lb @ 0 °   4.40 lb @ 90 ° |
|--|---------------------------------|

## Optical Specifications

|                   |                 |
|-------------------|-----------------|
| <b>Fiber Mode</b> | Multimode       |
| <b>Fiber Type</b> | OM5, LazrSPEED® |

## Environmental Specifications

|   |                                      |
|---|--------------------------------------|
| <b>Operating Temperature</b>                        | -10 °C to +60 °C (+14 °F to +140 °F) |
| <b>EN50575 CPR Cable EuroClass Fire Performance</b> | B2ca                                 |
| <b>Environmental Space</b>                          | Dual Rated LSZH/Riser   Indoor       |

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |

# U4VQXLUTN

---

ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted



## Included Products

- 760253115 N-192-MP-5G-F08LM/20T/B2 – Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk, 192 fiber with 2.0 mm Subunits, Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color, B2ca Flame rating
- 860658162 – 2.0 mm LC Uniboot GEN 1.5, Lime Green
- 860659021 – MPO8, LL, MALE, OM5, LIME, 2MM