

# SA-B10

---



Stiff Arm / Tieback Bracket, includes 126" pipe

## Product Classification

**Product Type** Stiff arm mount

## General Specifications

**Mounting** Round and angle legs

**Pipe, quantity** 1

## Dimensions

**Height** 203.2 mm | 8 in

**Width** 203.2 mm | 8 in

**Length** 3,200.4 mm | 126 in

**Pipe Length** 3,200.4 mm | 126 in

**Mounting Diameter, maximum** 88.9 mm | 3.5 in

**Mounting Diameter, minimum** 48.26 mm | 1.9 in

**Pipe Outer Diameter** 60.96 mm | 2.4 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Attachment hardware | Pipe

**Packaging quantity** 1

**Weight, net** 22.135 kg | 48.8 lb

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

ISO 9001:2015

### Classification

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

# SA-B10

---

ROHS Compliant/Exempted  
UK-ROHS Compliant/Exempted



## Included Products

- SA-B – Stiff Arm /Tieback Brackets for 2-3/8 in OD pipe - Pipe not included

# SA-B

---



Stiff Arm /Tieback Brackets for 2-3/8 in OD pipe - Pipe not included

## Product Classification

**Product Type** Stiff arm mount

## General Specifications

**Mounting** Round and angle legs

**Pipe, quantity** 0

## Dimensions

**Height** 152.4 mm | 6 in

**Width** 203.2 mm | 8 in

**Length** 203.2 mm | 8 in

**Mounting Diameter, maximum** 88.9 mm | 3.5 in

**Mounting Diameter, minimum** 48.26 mm | 1.9 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Attachment hardware | Brackets

**Packaging quantity** 1

**Weight, net** 8.301 kg | 18.3 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

