MPOPTIMATE-MODULES



MPOptimate® Universal Connectivity Platform (UCP), Q-Fit Fiber Modules

- The MPOptimate cassettes meet and exceed the attenuation and return loss specifications for datacenter applications
- Each MPOptimate cassette has a front plate with either LC, SC, MPO style adaptors that allows labeling of the ports
- The back plate of the MPOptimate cassette has one or two 12 fiber version MPO connections

CommScope's MPOptimate cassettes are designed for Data Center solutions supporting the topologies as specified in the data center standards EN50173-5 and ISO/IEC 24764. MPOptimate cassettes connected with MPO trunk or patch cables provide the possibility to make cross-connections or inter-connections to end equipment.

MPOptimate cassettes exist in 3 connector styles: MPO/LC, MPO/SC and MPO/MPO all in straight and pair flipped wire map. MPOptimate cassettes are designed to fit in the 19 inch UCP Modular MPO panel that accepts up to 4 MPO Quick-Fit Cassettes. The Quick-Fit MPO cassettes have port labels (included) and port ID strips. The labels are protected by a transparent cover.

Product Classification

Regional Availability Asia | EMEA | Latin America | North America

Product Type Fiber module

Product Brand MPOptimate®

Product Series UCP

General Specifications

Functionality Breakout

Application For use with Universal Connectivity Product (UCP) panels

Color, frontBlackColor, housingBlackColor, rearBlack

Interface, front LC/APC | LC/UPC | MPO | SC/APC | SC/UPC

Interface, rear MPO

