

TF-M4S2-8



Tower Face Mount with dual 8 ft x 4-1/2 in OD face pipe supports, includes pipe

Product Classification

Product Type Tower face mount

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

Pipe, quantity 1

Tower Taper Non-tapered | Tapered

Dimensions

Height 2,438.4 mm | 96 in

Face Width 2,438 m | 8 ft

Width 2,438.4 mm | 96 in

Length 304.8 mm | 12 in

Pipe Length 2,438.4 mm | 96 in

Face Support Pipe Diameter 114.3 mm | 4.5 in

Mounting Diameter, maximum 203.2 mm | 8 in

Mounting Diameter, minimum 0 mm | 0 in

Pipe Outer Diameter 114.3 mm | 4.5 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

TF-M4S2-8

Included	Crossover plates Pipes Saddle mounts
Packaging quantity	1
Weight, net	304.497 kg 671.3 lb

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--